SIEMENS

X-ray diffraction tubes special announcement

Siemens is excited to announce new pricing for its X-ray diffraction tubes! Check out our competitive prices and new warranty. We guarantee these products to be free from defect under normal use for a period of one year from date of installation or for 18 months from shipment, *regardless of hours of use*. This gives you the option of having a spare tube available on site for minimum downtime, and lets you meet ISO 9000 requirements!

All tubes made by Siemens, with our full backing. No third party vendors to deal with! We are fully staffed to answer all technical questions.

For more information, call the Siemens Service Department at 800-234-XRAY, or fax 608-276-3015.

Diffraction Standards Reference background and Zero-background Sample Plates Custom Designed and Built for any Application Your first step to improved x-ray diffraction results should be to dontact The Gem Dugout for quality diffraction alignment standards and And the next step is successful ero-background plates. ray diffraction results. Gem Dugout ton Drive

Now Available from ICDD

EDD

1993 ELECTRON DIFFRACTION DATA BASE

(NIST/Sandia/ICDD) Crystallographic & chemical data on more than 81,500 materials with search/match software for identification by electron diffraction methods*

CDF

1994 NIST CRYSTAL DATA FILE

Crystallographic & chemical data on more than 197,600 materials with retrieval software**

*Available for IBM-PC compatibles, VAX, Alpha AXP, and Macintosh **Available for IBM-PC compatibles, VAX, and Alpha AXP



INDEX TO ADVERTISERS

Diffraction Technology A1
Gem Dugout 234
Huber Diffraktionstechnik GmbH A2
ICDD A4, A6, 234
IC Laboratories A7
Philips Analytical X-Ray A8
Rigaku
Rontgenanalytik
Scintag Cover 4
Seifert X-Ray Corp Cover 3
Siemens Analytical Cover 2, 234
Spex Industries A7

Advertising Sales Office

American Institute of Physics 500 Sunnyside Boulevard Woodbury, NY 11797-2999 Telephone: (516) 576-2440 Advertising Fax: (516) 576-2481

Advertising Manager:
Advertising Representative:
Production:

Richard T. Kobel Nancy Kuhle Marcia Schlissel

XRD TUBES

SEIFERT

- Extra large and extra thin Be-window for a high intensity X-ray beam, specially suited for long fine focus applications.
- Razor sharp focal spots ensure beam brilliance.
- Spectral purity
- Efficient cooling system for extended anode life.
- Full line of tubes 5 different focal spots, 7 different target materials, 2 different anode lengths. compatible with European style towers.
 - Designed and manufactured under ISO 9001 standards. Backed by a world wide warranty of 2500 hrs.



World wide fast and friendly service, available through SEIFERT authorized service stations and re-sellers.



On the Internet: sxc1965@aol.com



SEIFERT X-RAY CORPORATION

TEL 610-539-4700 · TWX 510-660-0568 ·

2551Industry Lane > P.O. Box 294 · Fairview Village · Pennsylvania 19409

The Scintag Peltier X-ray Detector: The New Industry Standard in X-ray Diffraction

Another first from Scintag!

Scintag's exclusive second-generation Peltier-cooled x-ray detector for powder diffractometers is a breakthrough in x-ray diffraction. Without the need for liquid nitrogen cooling, Scintag's new detector provides all of the benefits of a solid state detector and more:

SCINTAG NC. USA

- Better sensitivity
- Superior peak-to-background ratios
- No alignment required
- No routine maintenance required

For the latest innovations in powder diffraction, Scintag is the clear choice. Contact us today for our brochure and a complete system demonstration, and judge for yourself.

SCINTAG. Inc.

707 Kifer Road • Sunnyvale, CA 94086 USA Tel. (408) 737-7200 • Fax (408) 737-9841



6